

LOW-VOLTAGE HEADS

Mini Om Head

DESCRIPTION

Flexible, clean head rotates 360°; pivots 260° to direct the beam. Low-voltage, MR16 lamp of up to 50 watts (not included). Accessory required; sold separately.

INSTALLATION


Socket terminates with FreeJack male connector, which may be installed into a system connector. Elements ordered with a system prefix include a connector for that system.

ACCESSORIES & OPTICAL CONTROLS

Mini Om Accessory

WEIGHT

0.31-2.28lb / 0.14-1.03kg ±



ORDERING INFORMATION

700 SYSTEM	OM	LENGTH (A)	FINISH
FJ	FREEJACK	03 3"	Z ANTIQUE BRONZE
MP	MONOPOINT	06 6"	S SATIN NICKEL
MO	MONORAIL	12 12"	
MO2	TWO-CIRCUIT MONORAIL	18 18"	
WMO	WALL MONORAIL		

Note: MP includes 4" Round Flush Canopy.



700 ____ OM ____

FIXTURE TYPE: _____

JOB NAME: _____

NOTES: _____
